

4ft		5-years warranty		Light source service life 40,000 hours (L85/Lumen maintenance factor 85%)		CRI-Ra85		Direct mounting type				Class	Type	Rating	Recessed type		
Class	Type	Rating	Light unit model name	Main unit model name	Total length 1216		Recessed hole 100 × 1215		Recessed hole 190 × 1217		Recessed hole 220 × 1235						
					EL-LHV41500-ID	EL-LHL40700-ID	EL-LHH41500-ID	EL-LHX42500-ID	EL-LHB41000A-ID	EL-LHB41900-ID	EL-LHB42200-ID						
				V-shape 150 width		Batten type		Reflector shade type		Bottom open type		100 in width		190 in width		220 in width	
FL36W/765 x 4 (FL36W/840 x 3) or equivalent 6,900lm	General Ra85	Fixed/Stepped dimming	EL-LU47023N-ID 2AHTN	MY-V470230/N-ID 2AHTN 5000K 6,900lm-43.0W-160.4lm/W	MY-L470230/N-ID 2AHTN 5000K 6,900lm-43.0W-160.4lm/W	MY-H470230/N-ID 2AHTN 5000K 6,900lm-43.0W-160.4lm/W	MY-X470230/N-ID 2AHTN 5000K 6,900lm-43.0W-160.4lm/W	FL36W/765 x 4 (FL36W/840 x 3) or equivalent 6,900lm	General Ra85	Fixed/Stepped dimming	MY-B470230/N-ID 2AHTN 5000K 6,900lm-43.0W-160.4lm/W	MY-B470232/N-ID 2AHTN 5000K 6,900lm-43.0W-160.4lm/W	MY-B470233/N-ID 2AHTN 5000K 6,900lm-43.0W-160.4lm/W				
		5-100% Dimming	EL-LU47023N-ID 2AHZ	MY-V470230/N-ID 2AHZ 5000K 6,900lm-43.0W-160.4lm/W	MY-L470230/N-ID 2AHZ 5000K 6,900lm-43.0W-160.4lm/W	MY-H470230/N-ID 2AHZ 5000K 6,900lm-43.0W-160.4lm/W	MY-X470230/N-ID 2AHZ 5000K 6,900lm-43.0W-160.4lm/W			5-100% Dimming	MY-B470230/N-ID 2AHZ 5000K 6,900lm-43.0W-160.4lm/W	MY-B470232/N-ID 2AHZ 5000K 6,900lm-43.0W-160.4lm/W	MY-B470233/N-ID 2AHZ 5000K 6,900lm-43.0W-160.4lm/W				
	Glare-cut Ra85	Fixed/Stepped dimming	EL-LU47020N-ID 2AHTN	MY-V470200/N-ID 2AHTN 5000K 6,900lm-36.7W-188.0lm/W	MY-L470200/N-ID 2AHTN 5000K 6,900lm-36.7W-188.0lm/W	MY-H470200/N-ID 2AHTN 5000K 6,900lm-36.7W-188.0lm/W	MY-X470200/N-ID 2AHTN 5000K 6,900lm-36.7W-188.0lm/W		Glare-cut Ra85	Fixed/Stepped dimming	MY-B470200/N-ID 2AHTN 5000K 6,900lm-36.7W-188.0lm/W	MY-B470202/N-ID 2AHTN 5000K 6,900lm-36.7W-188.0lm/W	MY-B470203/N-ID 2AHTN 5000K 6,900lm-36.7W-188.0lm/W				
		5-100% Dimming	EL-LU47025N-ID 2AHTN	MY-V470250/N-ID 2AHTN 5000K 5,800lm-43.0W-134.8lm/W	MY-L470250/N-ID 2AHTN 5000K 5,800lm-43.0W-134.8lm/W	MY-H470250/N-ID 2AHTN 5000K 5,800lm-43.0W-134.8lm/W	MY-X470250/N-ID 2AHTN 5000K 5,800lm-43.0W-134.8lm/W			5-100% Dimming	MY-B470250/N-ID 2AHTN 5000K 5,800lm-43.0W-134.8lm/W	MY-B470252/N-ID 2AHTN 5000K 5,800lm-43.0W-134.8lm/W	MY-B470253/N-ID 2AHTN 5000K 5,800lm-43.0W-134.8lm/W				
FL36W/765 x 3 (FL36W/840 x 2) or equivalent 5,200lm	General Ra85	Fixed/Stepped dimming	EL-LU45023N-ID 2AHTN	MY-V450230/N-ID 2AHTN 5000K 5,200lm-32.5W-160.0lm/W	MY-L450230/N-ID 2AHTN 5000K 5,200lm-32.5W-160.0lm/W	MY-H450230/N-ID 2AHTN 5000K 5,200lm-32.5W-160.0lm/W	MY-X450230/N-ID 2AHTN 5000K 5,200lm-32.5W-160.0lm/W	FL36W/765 x 3 (FL36W/840 x 2) or equivalent 5,200lm	General Ra85	Fixed/Stepped dimming	MY-B450230/N-ID 2AHTN 5000K 5,200lm-32.5W-160.0lm/W	MY-B450232/N-ID 2AHTN 5000K 5,200lm-32.5W-160.0lm/W	MY-B450233/N-ID 2AHTN 5000K 5,200lm-32.5W-160.0lm/W				
		5-100% Dimming	EL-LU45023N-ID 2AHZ	MY-V450230/N-ID 2AHZ 5000K 5,200lm-32.5W-160.0lm/W	MY-L450230/N-ID 2AHZ 5000K 5,200lm-32.5W-160.0lm/W	MY-H450230/N-ID 2AHZ 5000K 5,200lm-32.5W-160.0lm/W	MY-X450230/N-ID 2AHZ 5000K 5,200lm-32.5W-160.0lm/W			5-100% Dimming	MY-B450230/N-ID 2AHZ 5000K 5,200lm-32.5W-160.0lm/W	MY-B450232/N-ID 2AHZ 5000K 5,200lm-32.5W-160.0lm/W	MY-B450233/N-ID 2AHZ 5000K 5,200lm-32.5W-160.0lm/W				
	Glare-cut Ra85	Fixed/Stepped dimming	EL-LU45020N-ID 2AHTN	MY-V450200/N-ID 2AHTN 5000K 5,100lm-26.8W-190.2lm/W	MY-L450200/N-ID 2AHTN 5000K 5,100lm-26.8W-190.2lm/W	MY-H450200/N-ID 2AHTN 5000K 5,100lm-26.8W-190.2lm/W	MY-X450200/N-ID 2AHTN 5000K 5,100lm-26.8W-190.2lm/W		Glare-cut Ra85	Fixed/Stepped dimming	MY-B450200/N-ID 2AHTN 5000K 5,100lm-26.8W-190.2lm/W	MY-B450202/N-ID 2AHTN 5000K 5,100lm-26.8W-190.2lm/W	MY-B450203/N-ID 2AHTN 5000K 5,100lm-26.8W-190.2lm/W				
		5-100% Dimming	EL-LU45025N-ID 2AHTN	MY-V450250/N-ID 2AHTN 5000K 4,380lm-32.5W-134.7lm/W	MY-L450250/N-ID 2AHTN 5000K 4,380lm-32.5W-134.7lm/W	MY-H450250/N-ID 2AHTN 5000K 4,380lm-32.5W-134.7lm/W	MY-X450250/N-ID 2AHTN 5000K 4,380lm-32.5W-134.7lm/W			5-100% Dimming	MY-B450250/N-ID 2AHTN 5000K 4,380lm-32.5W-134.7lm/W	MY-B450252/N-ID 2AHTN 5000K 4,380lm-32.5W-134.7lm/W	MY-B450253/N-ID 2AHTN 5000K 4,380lm-32.5W-134.7lm/W				
FL36W/765 x 2 4,000lm	General Ra85	Fixed/Stepped dimming	EL-LU44023N-ID 2AHTN	MY-V440230/N-ID 2AHTN 5000K 4,000lm-24.9W-160.6lm/W	MY-L440230/N-ID 2AHTN 5000K 4,000lm-24.9W-160.6lm/W	MY-H440230/N-ID 2AHTN 5000K 4,000lm-24.9W-160.6lm/W	MY-X440230/N-ID 2AHTN 5000K 4,000lm-24.9W-160.6lm/W	FL36W/765 x 2 4,000lm	General Ra85	Fixed/Stepped dimming	MY-B440230/N-ID 2AHTN 5000K 4,000lm-24.9W-160.6lm/W	MY-B440232/N-ID 2AHTN 5000K 4,000lm-24.9W-160.6lm/W	MY-B440233/N-ID 2AHTN 5000K 4,000lm-24.9W-160.6lm/W				
System Lumen 3,200lm	General Ra85	Fixed/Stepped dimming	EL-LU43013N-ID 2AHTN	MY-V430130/N-ID 2AHTN 5000K 3,200lm-21.4W-149.5lm/W	MY-L430130/N-ID 2AHTN 5000K 3,200lm-21.4W-149.5lm/W	MY-H430130/N-ID 2AHTN 5000K 3,130lm-21.4W-146.2lm/W	MY-X430130/N-ID 2AHTN 5000K 3,100lm-21.4W-144.8lm/W	System Lumen 3,200lm	General Ra85	Fixed/Stepped dimming	MY-B430130/N-ID 2AHTN 5000K 2,970lm-21.4W-138.7lm/W	MY-B430132/N-ID 2AHTN 5000K 3,100lm-21.4W-144.8lm/W	MY-B430133/N-ID 2AHTN 5000K 3,100lm-21.4W-144.8lm/W				
		5-100% Dimming	EL-LU43013N-ID 2AHZ	MY-V430130/N-ID 2AHZ 5000K 3,200lm-21.4W-149.5lm/W	MY-L430130/N-ID 2AHZ 5000K 3,200lm-21.4W-149.5lm/W	MY-H430130/N-ID 2AHZ 5000K 3,130lm-21.4W-146.2lm/W	MY-X430130/N-ID 2AHZ 5000K 3,100lm-21.4W-144.8lm/W			5-100% Dimming	MY-B430130/N-ID 2AHZ 5000K 2,970lm-21.4W-138.7lm/W	MY-B430132/N-ID 2AHZ 5000K 3,100lm-21.4W-144.8lm/W	MY-B430133/N-ID 2AHZ 5000K 3,100lm-21.4W-144.8lm/W				
FL36W/840 x 1 or equivalent 2,500lm	General Ra85	Fixed/Stepped dimming	EL-LU42513N-ID 2AHTN	MY-V425130/N-ID 2AHTN 5000K 2,500lm-17.4W-143.6lm/W	MY-L425130/N-ID 2AHTN 5000K 2,500lm-17.4W-143.6lm/W	MY-H425130/N-ID 2AHTN 5000K 2,440lm-17.4W-140.2lm/W	MY-X425130/N-ID 2AHTN 5000K 2,420lm-17.4W-139.0lm/W	FL36W/840 x 1 or equivalent 2,500lm	General Ra85	Fixed/Stepped dimming	MY-B425130/N-ID 2AHTN 5000K 2,320lm-17.4W-133.3lm/W	MY-B425132/N-ID 2AHTN 5000K 2,420lm-17.4W-139.0lm/W	MY-B425133/N-ID 2AHTN 5000K 2,420lm-17.4W-139.0lm/W				
FL36W/765 x 1 2,000lm	General Ra85	Fixed/Stepped dimming	EL-LU42013N-ID 2AHTN	MY-V420130/N-ID 2AHTN 5000K 2,000lm-13.6W-147.0lm/W	MY-L420130/N-ID 2AHTN 5000K 2,000lm-13.6W-147.0lm/W	MY-H420130/N-ID 2AHTN 5000K 1,960lm-13.6W-144.1lm/W	MY-X420130/N-ID 2AHTN 5000K 1,940lm-13.6W-142.6lm/W	FL36W/765 x 1 2,000lm	General Ra85	Fixed/Stepped dimming	MY-B420130/N-ID 2AHTN 5000K 1,860lm-13.6W-136.7lm/W	MY-B420132/N-ID 2AHTN 5000K 1,940lm-13.6W-142.6lm/W	MY-B420133/N-ID 2AHTN 5000K 1,940lm-13.6W-142.6lm/W				

Common specifications: A: Voltage (compatible with 200 to 242V) Average color rendering index: Ra85 Light source lifetime: 40,000 hours Lumen maintenance factor 85%
 *The marks 5000K 3000K the lighting color temperature
 *Please note that the light unit luminous flux varies depending on the difference of the light color (color temperature)
 *Please note that the light color and illuminance may vary due to some variance in LED elements built in the unit of the same model.